

Floor Pressure Mat

Part No. OT644



Overview

- A durable 90cm x 60cm (3ft x 2ft) floor pressure mat c/w 2m lead and 6.35mm jack plug.
- Designed to trigger a Standard call on a Quantec or 800 Series Call System when foot pressure is detected.
- Typically located alongside a bed to alert staff to the prospect of a wandering patient in nursing homes, etc. Can also be used in lowlevel access control applications.
- Tough, durable grey PVC finish with a non-slip rubber base.
- Simple and reliable operation
- Connects to the 6.35mm remote socket on compatible Quantec and 800 Series call points. If connecting to a Quantec-Pro call point, a QP805G1A (6.5mm to RJ12) adaptor is also required.



More Information

Technical Specifications

Compatibility C-TEC's Quantec and 800 Series Call Systems.

Quiescent current

Alarm current Determined by the type of control equipment and number / type of field devices connected to the system.

Reassurance LED on host call point will illuminate steady when the floor pressure mat is activated and/or Indicators

its 6.35mm jack plug is removed.

Connections 6.35mm (quarter inch) jack plug.



T 01942 322744

E sales@c-tec.co.uk

















Onboard Sounder No, Onboard Infrared Receiver No. TBC. Construction & finish IP Rating IP41.

90~W~x~60~H~x~5~D~mm. 2m~long~lead. Dimensions

Weight TBC.

Operating conditions/temperature -5° C to $+40^{\circ}$ C. Max. relative humidity 95% non-condensing. Notes Can be wiped-clean using a non-caustic sanitising solution.















